

Cool solutions to thermal problems.

Rocky
Research

COMMERCIAL | INDUSTRIAL | DEFENSE

CIM03600

Up to 3,600 lbs. of ice daily

Automatic Bagging &
Sealing

Stores up to 1,200 lbs. of
bagged ice

10 lbs. bags of ice

Operates in up to 130°F
environment

Energy Efficient
Minimal operator input

Easy Setup

Easy Access

Easy Maintenance

Self-Purging Mode

ICE® Technology



CONTAINERIZED ICE MAKER SYSTEM



Utilizing Rocky Research's patented, state-of-the-art refrigeration technologies the **CIM03600** offers a highly reliable ice production, bagging, and storage system ready to address the rigors of harsh military environments.

Completely packaged within an ISO Tricon container and transportable by standard means. The **CIM03600** is easily setup by simply connecting to standard military 15kW generator or shore power and potable water. Designed to operate in high ambient temperatures up to 130°F the **CIM03600** is capable of supporting 40° to 90° inlet water with no degradation in its capacity. The **CIM03600** is able to produce up to 3600 pounds of sealed 10-pound bags of ice per day with the capacity to store up to 1200 pounds of bagged ice within the container.

The **CIM03600** requires minimal operator input while offering easy access and maintenance features including a self-purging mode.

System Specifications

Frequency:	50/60 Hz
Voltage:	208/230 VAC
Phase:	3 Phase
Power Connection:	100 Amp Class L Connector
*Fuel Usage:	22 gal. diesel or 26 gal. JP8 per 24 operational hours
Max. Ambient Temperature:	130°F
Refrigerant:	R407C

Physical Specifications

Form Factor:	ISO Tricon Container
Dimensions:	6'5.5" W x 8.0' H x 8.0' D
Weight:	~8,500 lbs.
**Water Supply Connection:	¾" NH-F hose bib (standard garden hose)

Environmental Specifications

Ambient Temperature (Hot):	MILSTD-810G, Method 505.5 (Procedures I)	✓	COMPLETED
Solar Radiation (watts/m ²):	MILSTD-810G, Method 505.5.1	✓	COMPLETED
Ambient Humidity (Hot):	MILSTD-810G, Method 507.5	✓	COMPLETED
Fungus:	MILSTD-810, Method 508.6	✓	COMPLETED
Salt Fog:	MILSTD-810G, Method 509.5	✓	COMPLETED
Blowing Dust & Sand:	MILSTD-810G, Method 510.5 (Procedures I & II)	✓	COMPLETED
Vibration:	MIL-STD-810G, Method 514.6	✓	COMPLETED
Shock:	MILSTD-810, Methods 516.6 & 526 Rail Impact Road March	✓	COMPLETED

*Average fuel usage when CIMS unit is powered by auxiliary 15kW generator.

**Water supply not required to be pressurized. CIMS can accept 40° to 90°F inlet water. Average water usage 500 gal. per 24 operational hours.

ICE® Intelligently Cooled Electronics is a registered trademark of Rocky Research. Microsoft and Windows are registered trademarks of Microsoft Corporation. Intel is a registered trademark of Intel Corporation. Other brands and product names are trademarks of their respective owners. Rocky Research believes the information in this publication is accurate as of its publication date. Such information is subject to change without notice and is subject to applicable technical product descriptions. Rocky Research is not responsible for inadvertent errors.